


Specifications

Product name		350PC Smart XMΩX			
Model		350PCS-XM OMEGAX			
Number of controlled axes		3 axes			
Control method		PTP control/interpolation control			
Working area X*Y		300×300 mm	400×400 mm	500×600 mm	700×800 mm
Working area Z		150 mm			
PTP operation speed setting range	X/Y	1 to 500 mm/s			
	Z	1 to 400 mm/s			
Interpolation operation speed setting range	X/Y	0.1 to 500 mm/s			
	Z	0.1 to 400 mm/s			
Repetitive positioning accuracy X/Y/Z		±0.005 mm			
Tool payload		8.7 kg			
Number of signal points	General-purpose input	19			
	General-purpose output	12			
Program capacity		300 recipes, 40,000 steps (999 channels)			
Program editing software		MuCAD™ V			
Software display language		Japanese/English/Chinese/Korean			
Main functions		3D alignment, work height measurement, nozzle height detection, offset, nozzle gap correction, automatic focus, log			
Interpolation		3D line, 3D circular arc/circular, 3D elliptical arc/ellipse, spline			
Options		Teaching pendant set, external operation box, holder units, signal tower, dispenser connection cable			
Rated voltage and frequency		Single phase, AC200-240 V, 50/60 Hz			
Power consumption		420 W			
Conformity standards		CE-marking (Machinery Directive, EMC Directive), EU RoHS			
Main unit dimensions (excluding protrusions)	Width (W)	831mm	931mm	1031mm	1239mm
	Depth (D)	671mm	771mm	971mm	1171mm
	Height (H)	630mm			
Main unit weight		80kg	91kg	120kg	143kg
Controller dimensions (excluding protrusions)		W450×D340×H265 mm			
Weight of dispense controller		18 kg			
350PCS control box dimensions (excluding protrusions)		W130×D280×H265 mm			
Weight of 350PCS control box		4.3 kg			

Outside drawings



 Safety precaution
Make sure to read the instruction manual before you use the unit, for your safety.

* We reserve the right to change the specifications without notice.
* All copyrights are retained by MUSASHI ENGINEERING. Reprinting, reproducing, and/or transmitting as electronic data in whole or in part these material without prior written permission is strictly prohibited.

MUSASHI ENGINEERING, INC. is certified and registered according to ISO14001 ENVIRONMENTAL MANAGEMENT.




<http://www.musashi-engineering.co.jp/english/>

World Leading Dispenser
MUSASHI ENGINEERING, INC.

HEAD OFFICE
8-7-4, Shimorenjaku, Mitaka, Tokyo, 181-0013, Japan TEL : (81)422-76-7111 / FAX : (81)422-76-7122
BRANCH
TOKYO, OSAKA, NAGOYA, SENDAI, FUKUOKA, SAITAMA, NAGANO, EAST-KANTO, AKITA, KANAZAWA

SINGAPORE 114 Lavender Street, #08-88/89 CT Hub 2, Singapore 338729
TEL : (65)6258-2422 / FAX : (65)6258-4844
THAILAND No.12 Soi Bangna-Trad 25, Bangna, Bangkok 10260 Thailand
TEL : (66)2-022-9015 / FAX : (66)2-769-5450
INDONESIA Jl. MH. Thamrin, Robson Square, Block A-15, Lippo Cikarang, Bekasi 17550, Jawa Barat, Indonesia
TEL : (62)21-8990-5005 / FAX : (62)21-8990-5004
GERMANY Leopoldstrasse 244, 1.Stock 80807 Munich Germany
TEL : (49)89-208039-470 / FAX : (49)89-208039-478
KOREA (902 No. 9 F. #C, Korea Bio Park.) 700, Daewangpangyo-ro, Bundang-gu, Seongnam-si, Gyeonggi-do 13488, Korea
TEL : (82)31-702-3811 / FAX : (82)31-702-3881
TAIWAN 8F-2, No. 158, Sec. 2, Gongdao 5th Road, Hsinchu, Taiwan 30070
TEL : (886)3-572-9200 / FAX : (886)3-572-9300

CHINA
HONG KONG Unit 1706, 17/F., Greenfield Tower.(South)Concordia Plaza, No.1 Science Museum Road, T.S.T.East, Kowloon, H.K.
TEL : (852)2620-5799 / FAX : (852)2620-5771
SHANGHAI A-120 Room, No.525 Xian Feng Street (No.55 Jin Yu Road), Min Hang, Shanghai, China
TEL : (86)21-6446-7881 / FAX : (86)21-6446-7882
SHENZHEN Room 702, West Tian'an Tech Plaza II, Tian'an Cyber Park, Futian District Shenzhen, China
TEL : (86)755-8346-6822 / FAX : (86)755-8346-6866
TIANJIN Room 1206, Sino Ocean International Center, No. 40 Huachang Road, Hedong District, Tianjin
TEL : (86)22-5856-2051
SUZHOU Room 1010, No.188 Wang Dun Road, GENWAY BUILDING, Suzhou City Industrial estate Distric, Jiangsu, CHINA
TEL : (86)512-6878-4428 / FAX : (86)512-6878-4438



Cartesian robot with PC control image recognition
IMAGE MASTER™
350PC Smart XMΩX




The fusion of dispensing “core” technologies
Inline 3D dispensing brings better quality!



Automatic correction for individual differences in works and pallet array errors


Complete 3-D alignment

Without alignment



Dispensing track

Tracing
(Z correction)




Complete correction of
device position deviation




Program generation/dispensing/measurement/log management


Applications




Dispensing on glass sides



Dispensing gaskets on motors



OCR dam dispensing



Dispensing adhesive on film


Field Network Supported
With CROSS MASTER™ QX specifications

◆ Yield improvement thanks to high-quality dispensing

Class-leading ± 0.005 mm repetitive positioning accuracy



Support for various work shapes
Edge-detection function
NEW

Position of works can be adjusted using image processing in a broader range of conditions, including works that could not be detected previously.



Coordination with dispenser
SynchroSpeed™ function
NEW PAT.P


Achieve a constant drawing width that is independent of robot speed. High-quality dispensing is implemented without the need for complicated adjustments.



Right-angle dispensing

Dispensing pattern editing software **MuCAD™**

- Switch product types instantly.
- Displayable DXF and Gerber file
- Automatically generates array program
- Automatically generates chip patterns on a wafer
- Easily divides into paint and no-paint areas



Aiming for higher dispensing quality

Strengthened linkage with the dispenser

- Able to dispense any complex shapes
- Available to change the dispensing condition setting for each dispensing point
- Eliminates difficult adjustment to help improve productivity

Improved operability

New teaching pendant

- Easy to transfer programs to multiple robots **NEW**



Multi-skill support

Enhanced hardware components

- No misalignment by closed loop control
- Prevents the robot head from falling during emergency stops
- Full connectivity, with 19 input and 12 output signals **NEW**
- Fast communication with **MuCAD™** **NEW**

Allows mounting of multiple dispensing units



With CROSS MASTER™ QX specifications